

## 

### **DESCRIPTION**

AMBEX AAC<sup>™</sup> anchoring capsules are a cementitious non-shrink grout designed for the anchoring of rebars or dowels in concrete, masonry or rock. This dry pre-mixed cement grout is encapsulated in a water permeable wrapping and once the grout capsule is saturated in water it becomes a fast setting thixotropic grout and is easily inserted in the anchoring hole.

AMBEX AAC<sup>™</sup> contain a mix of calcium aluminate cement, screened sand and selected additives.

#### **USES**

Can be used for civil engineering, architectural, mining or geological projects with plain, threaded or deformed rebars or dowels.

- Structural repairs
- Dams and tunnels
- Bridges
- Highway and airport slabs
- Wharves and canal structures
- Reservoirs and water structures
- Retaining or building walls
- Concrete formwork anchors
- Mining anchors
- Mining grout plugs for exploratory holes

#### **ADVANTAGES**

- Simple and economical
- Easy to install
- Easy handling and storage
- Reduces installation time and cost
- No product mixing on site
- No special tools and equipment required
- High early strengths
- Can be installed in cold weather at -17°C (0°F)
- Thixotropic mix
- Stable water/cement ratio
- No toxic emanation or fumes
- Environmentally friendly
- Does not contain calcium chloride
- Can be used underwater

#### **SIZES**

- 1. AMBEX AAC™ 13: 13 mm (1/2") diameter 200 mm (8") long
- 2. AMBEX AAC™ 19: 19 mm (3/4") diameter 300 mm (12") long
- **3. AMBEX AAC™ 25:** 25mm (1") diameter 300 mm (12") long
- Additional sizes available on special order
- Capsule placer available for AAC-25

#### **TECHNICAL INFORMATION**

Tests performed by independent laboratories.

			METRIC	IMPERIAL		
Water/Cement Ratio			0.32	0.32		
Net Weight (Dry)	AMBEX AAC $^{TM}$ – 25: AMBEX AAC $^{TM}$ – 19: AMBEX AAC $^{TM}$ – 13:		±240 g ±145 g ±50 g	± 0.5 lbs ± 0.3 lbs ± 0.1 lbs		
Density (Dry)			5-1.7 g/cm <sup>3</sup>	93.6-106.1 lbs/ft <sup>3</sup>		
Compressive (ASTM C-10	e Strength <i>28 (</i> 9)	days:	48.2 MPa	6990 psi		
Creep Test (ASTM E-1512)			Exceeds Requirements			
Soaking time			1 to 2 min			
Working time 20° C (68° F)			10 min			
Initial setting time (ASTM C-191)			6 min			
Final setting time (ASTM C-191)			26 min			
Expansion (ASTM C-1090)			0.05%			
Freeze-thaw resistance (ASTM C-(C-666, 312 cycles)			6) 10	0%		

## **PACKAGING**

	AAC-13	AAC-19	AAC-25
Capsules per bag	160	45	42
Weight per bag	8 kg/ 17.5 lbs	6.8 kg/15 lbs	10.3 kg/22.7 lbs
Bags per skid	132	180	132

## **GENERAL INFORMATION**

- Consult an engineer for structural design and capacity.
- Engineer must evaluate substrate and anchoring conditions.
- Contact an AMBEX representative if hole sizes and depths differ from chart.
- Underwater: Strength may be reduced by 30% depending on application.
- Cold weather applications may have slower initial setting time.

#### **SAFETY PRECAUTIONS**

This product contains cement and will react with water. It can inflame eyes and skin. In the case of direct contact with eyes, rinse several times with water, do not rub eyes and see a doctor. Wearing rubber gloves, dust-mask and safety glasses is highly recommended. Keep away from children. The Material Safety Data Sheet (MSDS) is available on request.

#### **STORAGI**

Cementitious material is sensitive to humidity. Store in a dry area where there is no humidity or freezing. Shelf life up to 2 years if well protected.

#### **GUARANTEE**

AMBEX CONCRETE TECHNOLOGIES INC. warrants that this product will perform as presented when used as described herein. AMBEX does not give any other implicit or explicit warranty. AMBEX's liability is limited to the replacement of the product proven defective.

#### AMBEX CONCRETE TECHNOLOGIES INC.

www.amb excorp.com

Ambex Concrete Technologies Inc. (AMBEX) guarantees that its products meet the technical specifications present on its data sheets. The products must be used as per directions stated on data sheets. AMBEX is not responsible for any damages resulting from improper use and application of its products. AMBEX's liability is limited to the replacement only if product is considered defective. AMBEX does not give any other warranty implicit or explicit, and cannot be held responsible for loss of profits, demands from third parties or any other damages.

Nominal rebar size	Recommended hole diameter mm (inch)	Capsule size mm (inch)	Embedment Depth mm (inch)	Fy Ultimate pullout strength KN	Fy Ultimate pullout strength lbs	Fy/F'y	Minimum embedment to develop yield strength of steel mm (inch)	F'y Yield strength of steel KN (lbs)*
10M (#3)	16 (5/8)	13 (1/2)	100 (4)	17.8	4001	0.45	146 (5-3/4)	40 (8990)
			125 (5)	28.9	6497	0.72		
			150 (6)	42.0	9442	1.05		
12M (#4) 19		13 (1/2)	100 (4)	21.5	4833	0.41	165 (6-1/2)	53 (11914)
	19 (3/4)		150 (6)	39.8	8947	0.75		
			200 (8)	83.8	18838	1.58		
		13 (1/2)	100 (4)	41.7	9374	0.52	184 (7-3/8)	80 (17984)
15M (#5)	19 (3/4)		150 (6)	64.0	14387	0.80		
(,			200 (8)	87.5	19670	1.09		
15M (#5)		19 (3/4)	100 (4)	48.4	10880	0.60	180 (7)	80 (17984)
	22 (7/8)		150 (6)	63.0	14255	0.79		
			200 (8)	91.3	20529	1.14		
20M (#6)	22 (7/8)	19 (3/4)	150 (6)	82.4	18524	0.69	190 (7-1/2)	120 (26977)
			200 (8)	131.6	29584	1.10		
			300 (12)	161.3	36260	1.34		
25M (#8)	28 (1-1/8)	25 (1)	200 (8)	215.6	48467	1.07	200 (8)	200 (44961)
			300 (12)	268.1	60269	1.34		
30M (#9)	38 (1-1/2)	25 (1)	300 (12)	364.0	81827	1.30	250 (10)	280 (62946)
			400 (16)	382.0	85874	1.36		
35M (#11)	42 (1-5/8)	25 (1)	300 (12)	398.4	89560	1.00	300 (12)	400 (89924)
			400 (16)	400**	89924**	1.00		

<sup>-</sup> The hole and rebar diameter may vary. Use the smallest hole diameter that allows easy insert of capsule and rebar

- Tests made at 28 days and 20° C (68° F)

- \* Steel 400 MPa (58000 psi)
- \*\*Hydraulic jack capacity: 400 KN (89923.58 lbs)

Tests made by Independant laboratory: Qualitas, Montreal, Quebec, Canada

# ESTIMATE OF THE NUMBER OF CAPSULES REQUIRED FOR YOUR PROJECT

## **CALCULATION FORMULA FOR ESTIMATE:**

 $N = \{3,142*L((D/2)^2 - (R/2)^2)\} \div V$ 

R: Rebar diameter in mm (inch)

D: Hole diameter in mm (inch)

L: Hole depth in mm (inch)


V: V= 21,225 mm³ (1.3 in³) for **AMBEX AAC™** – 13 V= 72,600 mm³ (4.4 in³) for **AMBEX AAC™** – 19

 $V = 125,600 \text{ mm}^3 (7.7 \text{ in}^3) \text{ for AMBEX AAC}^{TM} - 25$ 

N: Minimum number of capsules required (estimate)

## **RECOMMENDED INSTALLATION PROCEDURE**

- 1. DRILL ANCHORING HOLES: Drill holes as per recommended minimum dimensions in above table. *Use rotary percussion hammer with carbide bits.* Do not use diamond core bits. For faster and easier installation, increase hole diameter up to 6 mm (1/4") greater than the bar diameter for bars up to 25M (#8). Contact an AMBEX representative for different hole sizes and lengths.
- **2. CLEAN ANCHORING HOLES:** The hole must be clean before inserting the grout capsule. Clean with water pressure or air pressure to eliminate all dust and contaminants. Clean holes from bottom out. Residual water must be removed. Anchoring holes must be clean prior to inserting the **AMBEX AAC**™.



- 4. INSERT THE GROUT CAPSULE IN THE ANCHORING HOLE: Working time of the grout capsule is about 10 minutes at 20°C (68°F). Twist off end with staple and insert open end in hole. Do not remove the wrapping of the grout capsule. A capsule can be cut to required length when an anchoring hole does not require a full capsule. The remaining part can be used for another anchoring hole. CAUTION: Volume of grout required to fill hole may vary due to diameter and length of hole, cavities, fissures and nature of substrate. User must ensure that grout completely fills hole and encapsulates bar at surface after insertion of bar.
- **5. INSERT BAR IN THE ANCHORING HOLE:** Insert bar without rotating it through the capsule that is already in the hole. Use a hammer or percussion hammer/drill if required. Do not touch or move bar before final setting time. **Do not rotate rebar.**

## **TECHNICAL SERVICE**

AMBEX CONCRETE TECHNOLOGIES INC.
1522 Blvd. des Laurentides,
Laval, Quebec, Canada H7M 2N7
Tel. 450.662.9147 Toll free 1.888.351.7585
Fax 450.662.9013 www.ambexcorp.com
Questions? E-mail us at ambexinfo@ambexcorp.com
@2012. ALL RIGHTS RESERVED. AMBEX CONCRETE TECHNOLOGIES INC. (01/13/2012)



<sup>-</sup> Concrete compressive strength > 35 MPa (5080 psi)